



TL-D Colored

TL-D Colored 36W Yellow 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息		控制和调光	
底盖	G13 [Medium Bi-Pin Fluorescent]	可调光	是
50% 故障条件下的使用寿命 (标称)	15,000 小时		
灯技术		机械和外壳	
颜色代码	160	灯泡外形	T8 [26 毫米 (T8)]
光通量	1,580 lm		
颜色名称	黄色	审批和申请	
		汞 (Hg) 含量 (标称)	13.0 mg
		能耗 kWh/1000 h	44 kWh
操作和电气		产品数据	
功耗	36.0 W	订单产品名称	TL-D Colored 36W Yellow 1SL/25
灯具电流 (标称)	0.440 A	完整的产品名称	TL-D Colored 36W Yellow 1SL/25
电压 (标称)	103 V	完整产品代码	871150072751040
电压 (标称)	103 V	订购代码	928048501605
		材料编号 (12NC)	928048501605

TL-D Colored

计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500727510
计算器 - 每个外包装箱中的包数	25


EAN/UPC - 案例	8711500727527
--------------	---------------

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 36W Yellow 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据



Spectral Power Distribution Colour - TL-D Colored 36W Yellow 1SL/25

