



# TL-D Standard Colours

## TL-D 36W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	13,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)

Light Technical	
Color Code	54-765
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	72

Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]

Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	43 kWh


Product Data	
Order product name	TL-D 36W/54-765 1SL/25
Full product name	TL-D 36W/54-765 1SL/25
Full product code	871150070271540
Order code	928048505436
Material Nr. (12NC)	928048505436
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500702715
Numerator - Packs per outer box	25

# TL-D Standard Colours

EAN/UPC - Case


8711500727763

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/54-765 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

## Photometric data




Spectral Power Distribution Colour - TL-D 36W/54-765 1SL/25

## Lifetime




Life Expectancy Diagram - TL-D 36W/54-765 1SL/25



Life Expectancy Diagram - TL-D 36W/54-765 1SL/25

## TL-D Standard Colours

### Lifetime



Lumen Maintenance Diagram - TL-D 36W/54-765 1SL/25

