



# TL-D Blacklight Blue

## TL-D 36W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Useful Life (Nom)	12,000 hour(s)
Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.44 A
Voltage (Nom)	103 V
Voltage (Nom)	103 V
Mechanical and Housing	
Bulb Shape	T26 [T 26mm]

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
UV	
UV-A Radiation 100Hr (IEC)	9.5 W
Product Data	
Order product name	TL-D 36W BLB 1SL/25
Full product name	TL-D 36W BLB 1SL/25
Full product code	871150095115140
Order code	928048510805
Material Nr. (12NC)	928048510805
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500951151
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500951168


TL-D Blacklight Blue

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-D 36W BLB 1SL/25

