



# MASTER TL-D Reflex

## MASTER TL-D Reflex 58W/840 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,240 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89.6 lm/W
Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	58.5 W
Lamp Current (Nom)	0.670 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Reflector

Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	MST TL-D Reflex 58W/840 1 SLV/25
Full product name	MASTER TL-D Reflex 58W/840 1SL/25
Full product code	871150055962340
Order code	55962340
Material Nr. (12NC)	928048908479
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559623
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500559630


MASTER TL-D Reflex

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 58W/840 1 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 58W/840 1 SLV/25

Lifetime




Life Expectancy Diagram - MST TL-D Reflex 58W/840 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 58W/840 1 SLV/25

MASTER TL-D Reflex

Lifetime



Lumen Maintenance Diagram - MST TL-D Reflex 58W/840 1 SLV/25

