



MASTER TL-D Reflex

MST TL-D Reflex 58W/865 1 SLV/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15,000 hour(s)	Mechanical and Housing	
Light Technical		Bulb Finish	Reflector
Color Code	865 [CCT of 6500K]	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	5,000 lm	Approval and Application	
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)	5.0 mg
Correlated Color Temperature (Nom)	6500 K	Energy Consumption kWh/1000 h	68 kWh
Luminous Efficacy (rated) (Nom)	85.5 lm/W	Product Data	
Color rendering index (CRI)	>80	Order product name	MST TL-D Reflex 58W/865 1 SLV/25
Operating and Electrical		Full product name	MST TL-D Reflex 58W/865 1 SLV/25
Power Consumption	58.5 W	Full product code	871150026033840
Lamp Current (Nom)	0.670 A	Order code	928048986579
		Material Nr. (12NC)	928048986579
		Local order code	9280-489-86578

MASTER TL-D Reflex

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260338
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500260345
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 58W/865 1 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 58W/865 1 SLV/25

Lifetime




Life Expectancy Diagram - MST TL-D Reflex 58W/865 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 58W/865 1 SLV/25

MASTER TL-D Reflex

Lifetime



Lumen Maintenance Diagram - MST TL-D Reflex 58W/865 1 SLV/25

