



# MASTER TL-D Reflex

## MST TL-D Reflex 58W/865 1 SLV/25

The MASTER TL-D Reflex lamp directs most of the light to where you need it, thanks to an internal reflector. This results in having the same lighting level while using only half the number of lamps in the luminaire. It is therefore extremely suitable for use in luminaires with only a simple reflector or without any.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

<b>General Information</b>		<b>Controls and Dimming</b>	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15,000 hour(s)		
<b>Light Technical</b>		<b>Mechanical and Housing</b>	
Color Code	865 [CCT of 6500K]	Bulb Finish	Reflector
Luminous Flux	5,000 lm	Bulb Shape	T8 [26 mm (T8)]
Color Designation	Cool Daylight	<b>Approval and Application</b>	
Correlated Color Temperature (Nom)	6500 K	Mercury (Hg) Content (Nom)	5.0 mg
Luminous Efficacy (rated) (Nom)	85.5 lm/W	Energy Consumption kWh/1000 h	68 kWh
Color rendering index (CRI)	>80	<b>Product Data</b>	
<b>Operating and Electrical</b>		Order product name	MST TL-D Reflex 58W/865 1 SLV/25
Power Consumption	58.5 W	Full product name	MST TL-D Reflex 58W/865 1 SLV/25
Lamp Current (Nom)	0.670 A	Full product code	871150026033840
		Order code	928048986579
		Material Nr. (12NC)	928048986579
		Numerator - Quantity Per Pack	1

MASTER TL-D Reflex


EAN/UPC - Product/Case	8711500260338
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500260345

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL-D Reflex 58W/865 1 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MST TL-D Reflex 58W/865 1 SLV/25

Lifetime



Life Expectancy Diagram - MST TL-D Reflex 58W/865 1 SLV/25



Life Expectancy Diagram - MST TL-D Reflex 58W/865 1 SLV/25

## MASTER TL-D Reflex

### Lifetime

Lumen Maintenance Diagram - MST TL-D Reflex 58W/865 1 SLV/25

