



TL-D 标准颜色

TL-D 58W/54-765 1SL/25

低压汞放电灯，带有一个 26mm 的管状包层。

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
50% 故障条件下的使用寿命 (标称)	13,000 小时
灯技术	
颜色代码	54-765
光通量	4,000 lm
颜色名称	冷日光
相关色温 (标称)	6200 K
显色指数 (CRI)	72
操作和电气	
功耗	58.5 W
灯具电流 (标称)	0.670 A
电压 (标称)	111 V
电压 (标称)	111 V
控制和调光	
可调光	是

机械和外壳	
灯泡外形	T8
审批和申请	
汞 (Hg) 含量 (标称)	5.0 mg
能耗 kWh/1000 h	68 kWh
产品数据	
订单产品名称	TL-D 58W/54-765 1SL/25
完整的产品名称	TL-D 58W/54-765 1SL/25
完整产品代码	692234199605400
订购代码	928049005453
材料编号 (12NC)	928049005453
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6922341996054
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	6922341996511


TL-D 标准颜色

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

光度数据




Spectral Power Distribution Colour - TL-D 58W/54-765 1SL/25

寿命




Life Expectancy Diagram - TL-D 58W/54-765 1SL/25



Life Expectancy Diagram - TL-D 58W/54-765 1SL/25

TL-D 标准颜色

寿命



Lumen Maintenance Diagram - TL-D 58W/54-765 1SL/25

