



MASTER CosmoWhite CPO-TT Xtra

MST CosmoWhite CPO-TT Xtra 315W/830 E40

New-generation ceramic metal-halide tubular lamps used in outdoor applications, offering efficient and pleasant white light

安全提示

- Use only in a totally enclosed luminaire, even during testing (IEC 61167, IEC 62035, IEC 60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with suitable electronic control gear
- Control gear must include end-of-life protection (IEC 61167, IEC 62035)
- E27 lamp holders and other parts in luminaires should be designed to withstand the ignition voltage of the electronic control gear (rated at 5 kV ignition pulse)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底座	E40 [E40]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	30,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.426
色度坐标 Y (标称)	0.402
光效 (额定) (标称)	116 lm/W
显色指数 (CRI)	87


弧长 O (标称)	15.9 mm
操作和电气	
功耗	315.0 W
电压 (标称)	98 V
电压 (标称)	98 V
控制和调光	
可调光	是
机械和外壳	
灯泡外观	透明

MASTER CosmoWhite CPO-TT Xtra

灯泡外形	T46 [T 46 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	28.0 mg
能耗 kWh/1000 h	347 kWh
产品数据	
订单产品名称	MST CosmoWhite CPO-TT Xtra 315W/830 E40
完整的产品名称	MST CosmoWhite CPO-TT Xtra 315W/830 E40


完整产品代码	871869647753300
订购代码	928061109227
材料编号 (12NC)	928061109227
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718696477533
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718696477540

二维绘图




Product	D (max)	D	O	L	C (max)
MST CosmoWhite CPO-TT Xtra 315W/830 E40	47 mm	46 mm	15.9 mm	162 mm	257 mm

光度数据




Light Distribution Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40




Spectral Power Distribution Colour - MST CosmoWhite CPO-TT Xtra 315W/830 E40

MASTER CosmoWhite CPO-TT Xtra

寿命



Life Expectancy Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40



Lumen Maintenance Diagram - MST CosmoWhite CPO-TT Xtra 315W/830 E40

