



# MASTERColour CDM-TC Warm

## MASTERColour CDM-TC Warm 70W/925 G8.5

The world’s most efficient and lowest-cost accent lighting is to become available in highly efficient sparkling warm light. CDM Warm is the only light source that combines very warm light with near-perfect color rendering and very high efficacy.

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G8.5 [G8.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	925
Color Designation	Warm
Chromaticity Coordinate X (Nom)	0.460
Chromaticity Coordinate Y (Nom)	0.405
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	93


Arc Length O (Nom)	5 mm
Operating and Electrical	
Power Consumption	73.0 W
Voltage (Nom)	95 V
Voltage (Nom)	95 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

MASTERColour CDM-TC Warm

Bulb Shape	T14 [T 14 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	8.6 mg
Energy Consumption kWh/1000 h	80 kWh
Product Data	
Order product name	MASTERColour CDM-TC Warm 70W/925 G8.5
Full product name	MASTERColour CDM-TC Warm 70W/925 G8.5

Full product code	871829120307000
Order code	20307000
Material Nr. (12NC)	928061505131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291203070
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291203087

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERColour CDM-TC	15 mm	0.57	5 mm	51 mm	53 mm	52 mm	85 mm
Warm 70W/925 G8.5		inch					

Photometric data



Light Distribution Diagram - MASTERColour CDM-TC Warm 70W/925 G8.5

