



MASTERCoulour CDM-TC Evolution

MC CDM-TC Evolution 20W/930 G8.5

Single-ended, highest-efficiency, longest-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high color rendering

安全提示

- Use only in a totally enclosed luminaire, even during testing (IEC61167, IEC62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- The vast majority of drivers are fully compatible with CDM Evolution lamps. However, best performance is guaranteed with Philips drivers.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- CDM Evolution lamps are designed to comply with IEC standards
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	G8.5 [G8.5]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	25,000 小时

灯技术	
颜色代码	930 [CCT of 3000K]
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.43
色度坐标 Y (标称)	0.393
相关色温 (标称)	3000 K

光效 (额定) (标称)	102 lm/W
显色指数 (CRI)	90
弧长 O (标称)	3.6 mm


操作和电气	
功耗	20 W
电压 (标称)	105 V
电压 (标称)	105 V

MASTERCoulour CDM-TC Evolution

控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡外形	T14 [T 14 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	3.0 mg
能耗 kWh/1000 h	22 kWh
产品数据	
订单产品名称	MC CDM-TC Evolution 20W/930 G8.5



完整的产品名称	MC CDM-TC Evolution 20W/930 G8.5
完整产品代码	871829165920400
订购代码	928064805131
材料编号 (12NC)	928064805131
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718291659204
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291659211

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MC CDM-TC Evolution 20W/930 G8.5	15 mm	3.6 mm	51 mm	53 mm	52 mm	85 mm

光度数据





Light Distribution Diagram - MC CDM-TC Evolution 20W/930 G8.5

Spectral Power Distribution Colour - MC CDM-TC Evolution 20W/930 G8.5

MASTERC colour CDM-TC Evolution

寿命



Lumen Maintenance Diagram - MC CDM-TC Evolution 20W/930 G8.5

Life Expectancy Diagram - MC CDM-TC Evolution 20W/930 G8.5

