



# MASTER MHN-LA

## MASTER MHN-LA 1000W/956 230V XWH

Compact quartz metal halide lamps with double-pinch

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	X528
Operating Position	P5 [Parallel +/-5D or Horizontal(HOR)]
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	956 [CCT of 5600K]
Color Designation	Daylight
Chromaticity Coordinate X (Nom)	337
Chromaticity Coordinate Y (Nom)	331
Correlated Color Temperature (Nom)	5600 K
Luminous Efficacy (rated) (Nom)	86.0 lm/W
Color rendering index (CRI)	80
Arc Length O (Nom)	40.5 mm

Operating and Electrical	
Power Consumption	1,040.0 W
Voltage (Nom)	125 V

Voltage (Nom)	125 V
---------------	-------

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	TD40

Approval and Application	
Mercury (Hg) Content (Nom)	95 mg
Energy Consumption kWh/1000 h	1144 kWh


Product Data	
Order product name	MASTER MHN-LA 1000W/956 230V XWH
Full product name	MASTER MHN-LA 1000W/956 230V XWH
Full product code	871150020077800
Order code	928072205130
Material Nr. (12NC)	928072205130

# MASTER MHN-LA

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548218
Numerator - Packs per outer box	1


EAN/UPC - Case	8711500200778
----------------	---------------

## Dimensional drawing




Product	D (max)	O	X	A
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm

## Photometric data




Spectral Power Distribution Colour - MASTER MHN-LA 1000W/956 230V XWH

## Lifetime



Life Expectancy Diagram - MASTER MHN-LA 1000W/956 230V XWH



Lumen Maintenance Diagram - MASTER MHN-LA 1000W/956 230V XWH

