



MASTER MHN-LA

MASTER MHN-LA 2000W/956 400V XWH

Compact quartz metal halide lamps with double-pin

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	X528
Operating position	P5 [Parallel +/-5D or Horizontal(HOR)]
Life to 50% failures (nom.)	13,000 h

Light Technical	
Colour Code	956 [CCT of 5600K]
Colour designation	Daylight
Chromaticity Coordinate X (Nom)	330
Chromaticity Coordinate Y (Nom)	339
Correlated Colour Temperature	5600 K
Luminous efficacy (rated) (nom.)	93 lm/W
Colour rendering index (CRI)	82
Arc Length O (Nom)	108 mm

Operating and Electrical	
Power Consumption	2,040.0 W
Voltage (nom.)	225 V

Voltage (nom.)	225 V
----------------	-------

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	TD40

Approval and Application	
Mercury (Hg) content (nom.)	140 mg
Energy consumption kWh/1,000 hours	2244 kWh


Product Data	
Order product name	MASTER MHN-LA 2000W/956 400V XWH
Full product name	MASTER MHN-LA 2000W/956 400V XWH
Full EOC	871150020073000
Order code	20073000
Material no. (12 NC)	928072505130

MASTER MHN-LA

Local order code	2000MHNLA956
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291548225
Numerator – packs per outer box	1


EAN/UPC - Case	8711500200730
----------------	---------------

Dimensional drawing




Product	D (max)	O	X	A
MASTER MHN-LA 2000W/956 400V XWH	40 mm	108 mm	58 mm	353 mm

Photometric data




Spectral Power Distribution Colour - MASTER MHN-LA 2000W/956 400V XWH

Lifetime



Life Expectancy Diagram - MASTER MHN-LA 2000W/956 400V XWH



Lumen Maintenance Diagram - MASTER MHN-LA 2000W/956 400V XWH

