



# MASTER MHN-LA

## MASTER MHN-LA 1000W/842 230V XWH

Compact quartz metal halide lamps with double-pinch

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)	
Cap-Base	X528 [X528]	125 V	
Operating Position	P5 [Parallel +/-5D or Horizontal(HOR)]	Controls and Dimming	
Life to 50% Failures (Nom)	15,000 hour(s)	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	842 [CCT of 4200K]	Bulb Finish	Clear
Color Designation	Cool White (CW)	Bulb Shape	TD40 [TD 40mm]
Chromaticity Coordinate X (Nom)	366	Approval and Application	
Chromaticity Coordinate Y (Nom)	370	Mercury (Hg) Content (Nom)	112 mg
Correlated Color Temperature (Nom)	4200 K	Energy Consumption kWh/1000 h	1144 kWh
Luminous Efficacy (rated) (Nom)	92.00 lm/W	Product Data	
Color rendering index (CRI)	70	Order product name	MASTER MHN-LA 1000W/842 230V XWH
Arc Length O (Nom)	40.5 mm	Full product name	MASTER MHN-LA 1000W/842 230V XWH
Operating and Electrical		Full product code	871150020078500
Power Consumption	1,040.0 W	Order code	928073005130
Voltage (Nom)	125 V	Material Nr. (12NC)	928073005130

# MASTER MHN-LA

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548232
Numerator - Packs per outer box	1


EAN/UPC - Case	8711500200785
----------------	---------------

## Dimensional drawing




Product	D (max)	O	X	A
MASTER MHN-LA 1000W/842 230V XWH	40 mm	40.5 mm	35 mm	286 mm

## Photometric data




Spectral Power Distribution Colour - MASTER MHN-LA 1000W/842 230V XWH

## Lifetime



Life Expectancy Diagram - MASTER MHN-LA 1000W/842 230V XWH



Lumen Maintenance Diagram - MASTER MHN-LA 1000W/842 230V XWH

