



# HPI-T High Wattage

## HPI-T 2000W/542 E40 380V 1SL/4

Quartz metal halide lamps with clear outer bulb

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General Information                |                                          |
|------------------------------------|------------------------------------------|
| Cap-Base                           | E40                                      |
| Operating Position                 | P20 [Parallel +/-20D or Horizontal(HOR)] |
| Life to 50% Failures (Nom)         | 12,000 hour(s)                           |
| Light Technical                    |                                          |
| Color Code                         | 542 [CCT of 4200K]                       |
| Color Designation                  | Cool White (CW)                          |
| Chromaticity Coordinate X (Nom)    | 387                                      |
| Chromaticity Coordinate Y (Nom)    | 403                                      |
| Correlated Color Temperature (Nom) | 3800 K                                   |
| Luminous Efficacy (rated) (Nom)    | 101 lm/W                                 |
| Color rendering index (CRI)        | 59                                       |
| Arc Length O (Nom)                 | 120 mm                                   |
| Operating and Electrical           |                                          |
| Power Consumption                  | 1,980 W                                  |
| Voltage (Nom)                      | 232 V                                    |


|                               |                                |
|-------------------------------|--------------------------------|
| Voltage (Nom)                 | 232 V                          |
| Controls and Dimming          |                                |
| Dimmable                      | No                             |
| Mechanical and Housing        |                                |
| Bulb Finish                   | Clear                          |
| Bulb Shape                    | T100                           |
| Approval and Application      |                                |
| Mercury (Hg) Content (Nom)    | 256 mg                         |
| Energy Consumption kWh/1000 h | 2178 kWh                       |
| Product Data                  |                                |
| Order product name            | HPI-T 2000W/542 E40 380V 1SL/4 |
| Full product name             | HPI-T 2000W/542 E40 380V 1SL/4 |
| Full product code             | 871150020235245                |
| Order code                    | 928074209228                   |

HPI-T High Wattage

|                               |               |
|-------------------------------|---------------|
| Material Nr. (12NC)           | 928074209228  |
| Local order code              | HPIT2000380V  |
| Numerator - Quantity Per Pack | 1             |
| EAN/UPC - Product/Case        | 8711500202352 |


|                                 |               |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 4             |
| EAN/UPC - Case                  | 8711500202369 |

Dimensional drawing




| Product                        | D (max)  | O      | L      | C (max) |
|--------------------------------|----------|--------|--------|---------|
| HPI-T 2000W/542 E40 380V 1SL/4 | 101.5 mm | 120 mm | 267 mm | 430 mm  |

Photometric data




Spectral Power Distribution Colour - HPI-T 2000W/542 E40 380V 1SL/4

Lifetime



Life Expectancy Diagram - HPI-T 2000W/542 E40 380V 1SL/4



Lumen Maintenance Diagram - HPI-T 2000W/542 E40 380V 1SL/4

## HPI-T High Wattage

