



MSR

MSR 400 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | GX9.5 [GX9.5] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 1,000 hour(s) |
| Light Technical | |
| Color Code | - [Not Specified] |
| Luminous Flux (Min) | 28,440 lm |
| Luminous Flux | 31,600 lm |
| Chromaticity Coordinate X (Nom) | 326 |
| Chromaticity Coordinate Y (Nom) | 321 |
| Correlated Color Temperature (Nom) | 5830 K |
| Luminous Efficacy (rated) (Nom) | 79 lm/W |
| Color rendering index (CRI) | 95 |

| Arc Length O (Nom) | 6.0 mm |
|--------------------------|-----------------|
| Operating and Electrical | |
| Power Consumption | 400 W |
| Lamp Current (Nom) | 7 A |
| Controls and Dimming | |
| Dimmable | No |
| Product Data | |
| Order product name | MSR 400 1CT/4 |
| Full product name | MSR 400 1CT/4 |
| Full product code | 871869641600600 |
| Order code | 261388 |
| Material Nr. (12NC) | 928077905115 |

| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696416006 |
| Numerator - Packs per outer box | 4 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8718696416013 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F (max) | F | F (min) |
|---------|---------|-----|---------|---------|----|---------|---------|----|---------|
| MSR 400 | 23 mm | 6.0 | 61 mm | 63 mm | 62 | 112 mm | 36 mm | 35 | 34 mm |
| 1CT/4 | | mm | | | mm | | | mm | |

Photometric data



Spectral Power Distribution Colour - MSR 400 1CT/4

