



MASTERColour CDM-T

MASTERC CDM-T 150W/830 G12 1CT

系列单端紧凑型高光效放电灯在整个寿命期间具有稳定的光色和明亮通透的闪光

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底座	G12
操作位置	UNIVERSAL [任意或通用 (U)]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	12,000 小时
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	13,000 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K
光效 (额定) (标称)	88 lm/W


显色指数 (CRI)	88
弧长 O (标称)	9 mm
操作和电气	
功耗	150.1 W
电压 (标称)	96 V
电压 (标称)	96 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明

MASTERC colour CDM-T

灯泡外形	T19
审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	14.3 mg
汞 (Hg) 含量 (标称)	14.3 mg
能耗 kWh/1000 h	151 kWh
EPREL 注册号	473335
产品数据	
订单产品名称	MASTERC CDM-T 150W/830 G12 1CT


完整的产品名称	MASTERC CDM-T 150W/830 G12 1CT
完整产品代码	871150019780115
订购代码	928083705125
材料编号 (12NC)	928083705125
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500197801
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500197818

二维绘图




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 in	9 mm	55 mm	57 mm	56 mm	110 mm

光度数据





Light Distribution Diagram - MASTERC CDM-T 150W/830 G12 1CT



Spectral Power Distribution Colour - MASTERC CDM-T 150W/830 G12 1CT

MASTERC colour CDM-T

寿命



Life Expectancy Diagram - MASTER CDM-T 150W/830 G12 1CT

Lumen Maintenance Diagram - MASTER CDM-T 150W/830 G12 1CT

