



CDM

CDM-SA/R 150W/942

The perfect color rendering and long life of these Ceramic Discharge Metal-halide lamps make them ideal for fiber optics lighting systems in shop displays, decorative lighting and swimming pool illumination. They can be mounted in color changing projectors.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	CERAMICCAP-CABLE [Ceramic Cap-Cable (C)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	6,000 hour(s)
Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux (Min)	2,295 lm
Luminous Flux	2,550 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.366
Chromaticity Coordinate Y (Nom)	0.353
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	16.1 lm/W

Color rendering index (CRI)	96
Operating and Electrical	
Power Consumption	158.0 W
Lamp Current (Nom)	1.76 A
Voltage (Nom)	106 V
Voltage (Nom)	106 V
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	CDM-SA/R 150W/942 UNP/1
Full product name	CDM-SA/R 150W/942
Full product code	871150020150800

Order code	382788
Material Nr. (12NC)	928086805303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900783490


Numerator - Packs per outer box	1
EAN/UPC - Case	8711500201508

Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	3-3/4 inch	11-1/16 inch	4-3/16 inch

Photometric data



Spectral Power Distribution Colour – CDM-SA/R 150W/942 UNP/1

