



MASTERColour CDM-R

MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT

Range of compact, high-efficiency, discharge reflector lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. Color 830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	39.1 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Voltage (Nom)	85 V
Life to 50% Failures (Nom)	9,000 hour(s)	Voltage (Nom)	85 V
Light Technical		Controls and Dimming	
Color Code	942 [CCT of 4200K]	Dimmable	No
Beam Angle (Nom)	30 degree(s)	Mechanical and Housing	
Luminous Flux	1,900 lm	Bulb Finish	Clear
Luminous Intensity (Nom)	5,000 cd	Bulb Shape	PAR20 [PAR 2.5 inch/63mm]
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.375	Mercury (Hg) Content (Nom)	2.8 mg
Chromaticity Coordinate Y (Nom)	0.370		
Correlated Color Temperature (Nom)	4200 K		
Color rendering index (CRI)	92		

MASTERC colour CDM-R

Product Data	
Order product name	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT
Full product name	MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT
Full product code	872790088724200
Order code	928091600610
Material Nr. (12NC)	928091600610


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900887242
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900887259

Dimensional drawing




Product	D (max)	D	C (max)	C
MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT	65 mm	64 mm	92 mm	90 mm

Photometric data



Light Distribution Diagram - MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT



Spectral Power Distribution Colour - MASTERC CDM-R 35W/942 E26 PAR20 30D 1CT

