



# MASTERColour CDM-R111

## MASTERColour CDM-R111 20W/830 GX8.5 24D 1CT/6

The MASTERColour CDM-R111 combines the trendy look of the 111 mm aluminium reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

### Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Correlated Color Temperature (Nom)	3000 K
Cap-Base	GX8.5 [GX8.5]	Color rendering index (CRI)	87
Operating Position	UNIVERSAL [Any or Universal (U)]	LLMF At End Of Nominal Lifetime (Nom)	58 %
Switching Cycle	800	Luminous Flux in 90° Cone (Rated)	625 lm
Life to 50% Failures (Nom)	9,000 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	20 W
Color Code	830 [CCT of 3000K]	Warm-up time to 60% light	120 s
Beam Angle (Nom)	24 degree(s)	Voltage (Nom)	101 V
Luminous Intensity (Nom)	4,700 cd	Voltage (Nom)	101 V
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	0.438		
Chromaticity Coordinate Y (Nom)	0.392		

MASTERC colour CDM-R111

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Reflector
Bulb Shape	R111 [R 111mm]
Approval and Application	
Mercury (Hg) Content (Nom)	2.4 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Order product name	MASTERC CDM-R111 20W/830 GX8.5 24D 1CT/6


Full product name	MASTERC colour CDM-R111 20W/830 GX8.5 24D 1CT/6
Full product code	871150020951110
Order code	20951110
Material Nr. (12NC)	928093205330
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500209511
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500209528

Dimensional drawing




Product	D (max)	C (max)
MASTERC CDM-R111 20W/830 GX8.5 24D 1CT/6	111 mm	95 mm

Photometric data



Light Distribution Diagram - MASTERC CDM-R111 20W/830 GX8.5 24D 1CT/6



Spectral Power Distribution Colour - MASTERC CDM-R111 20W/830 GX8.5 24D 1CT/6

## MASTERColour CDM-R111

