



# MASTERColour CDM-T

## MASTERC CDM-T 35W/842 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G12 [G12]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	12,000 hour(s)

Light Technical	
Color Code	842 [CCT of 4200K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.370
Chromaticity Coordinate Y (Nom)	0.367

MASTERCoulour CDM-T

Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	84
Arc Length O (Nom)	5 mm

Operating and Electrical

Power Consumption	39.1 W
Voltage (Nom)	85 V
Voltage (Nom)	85 V

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19 [T 19mm]


Approval and Application

Mercury (Hg) Content (Nom)	2.7 mg
Energy Consumption kWh/1000 h	43 kWh

Product Data


Order product name	MASTERC CDM-T 35W/842 G12 1CT/12
Full product name	MASTERC CDM-T 35W/842 G12 1CT/12
Full product code	871869648445600
Order code	928094305129
Material Nr. (12NC)	928094305129
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696484456
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696484463

Dimensional drawing





Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 35W/842 G12 1CT/12	20 mm	0.75 inch	5 mm	55 mm	57 mm	56 mm	103 mm


Photometric data



Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12





Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12






MASTERC colour CDM-T

Photometric data



Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12


Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12



Light Distribution Diagram - MASTERC CDM-T 35W/842 G12 1CT/12

Spectral Power Distribution Colour - MASTERC CDM-T 35W/842 G12 1CT/12

Lifetime



Life Expectancy Diagram - MASTERC CDM-T 35W/842 G12 1CT/12

## MASTERColour CDM-T

