



MASTERColour CDM-T 精锐型

MASTERC CDM-T Elite 150W/930 G12 1CT/12

单端高光效陶瓷金属卤化物放电灯

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	G12 [G12]
操作位置	P10 [并行 +/-10D 或水平 (HOR)]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	12,000 小时
灯技术	
颜色代码	930 [CCT of 3000K]
光通量	14,600 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K
光效 (额定) (标称)	98 lm/W
显色指数 (CRI)	92

弧长 O (标称)	9 mm
操作和电气	
功耗	150.1 W
电压 (标称)	92 V
电压 (标称)	92 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡外形	T19 [T 19 毫米]

MASTERC colour CDM-T 精锐型

审批和申请	
能效等级	F
汞 (Hg) 含量 (最高)	9.5 mg
汞 (Hg) 含量 (标称)	9.5 mg
能耗 kWh/1000 h	151 kWh
EPREL 注册号	473357
产品数据	
订单产品名称	MASTERC CDM-T Elite 150W/930 G12 1CT/12
完整的产品名称	MASTERC CDM-T Elite 150W/930 G12 1CT/12

二维绘图




光度数据



Light Distribution Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12

完整产品代码	871150021312915
订购代码	928094705125
材料编号 (12NC)	928094705125
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500213129
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500213136


Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 150W/930 G12 1CT/12	20 mm	9 mm	55 mm	57 mm	56 mm	110 mm




Spectral Power Distribution Colour - MASTERC CDM-T Elite 150W/930 G12 1CT/12

MASTERColour CDM-T 精锐型

寿命



Life Expectancy Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12



Lumen Maintenance Diagram - MASTERC CDM-T Elite 150W/930 G12 1CT/12

