



ML

ML 250W E40 220-230V HG 1SL/12

混合光线光源

安全提示


· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	E40 [E40]
操作位置	VBU/VBD30 [垂直或底座朝上/底座朝下 +/-30D]
50% 故障条件下的使用寿命 (标称)	10,000 小时
灯技术	
色度坐标 X (标称)	403
色度坐标 Y (标称)	382
光效 (额定) (标称)	21 lm/W
显色指数 (CRI)	63
操作和电气	
功耗	260.0 W
电压 (标称)	225 V
电压 (标称)	225 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	镀膜玻璃



灯泡材料	硬玻璃
灯泡外形	ED90 [ED 90 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	14 mg
能耗 kWh/1000 h	286 kWh
产品数据	
订单产品名称	ML 250W E40 220-230V HG 1SL/12
完整的产品名称	ML 250W E40 220-230V HG 1SL/12
完整产品代码	871150018162615
订购代码	928096257296
材料编号 (12NC)	928096257296
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500181626
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8711500181633

二维绘图



Product	D (max)	C (max)
ML 250W E40 220-230V HG 1SL/12	91 mm	226 mm



光度数据



Light Distribution Diagram - ML 250W E40 220-230V HG 1SL/12

Spectral Power Distribution Colour - ML 250W E40 220-230V HG 1SL/12

寿命



Life Expectancy Diagram - ML 250W E40 220-230V HG 1SL/12

Lumen Maintenance Diagram - ML 250W E40 220-230V HG 1SL/12

