



MSR Hot Restrike

MSR 200 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


| General Information | | Color rendering index (CRI) | |
|------------------------------------|----------------------------------|-----------------------------|------------------|
| Cap-Base | GZY9.5 [GZY9.5] | Arc Length O (Nom) | 5.0 mm |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Operating and Electrical | |
| Life to 50% Failures (Nom) | 200 hour(s) | Power Consumption | 200 W |
| Light Technical | | Lamp Current (Nom) | 3.3 A |
| Color Code | - [Not Specified] | Controls and Dimming | |
| Luminous Flux (Min) | 12,000 lm | Dimmable | Yes |
| Luminous Flux | 15,000 lm | Product Data | |
| Chromaticity Coordinate X (Nom) | 325 | Order product name | MSR 200 HR 1CT/4 |
| Chromaticity Coordinate Y (Nom) | 323 | Full product name | MSR 200 HR 1CT/4 |
| Correlated Color Temperature (Nom) | 6000 K | | |
| Luminous Efficacy (rated) (Nom) | 75 lm/W | | |

MSR Hot Restrike

| | |
|-------------------------------|-----------------|
| Full product code | 871869641604400 |
| Order code | 261362 |
| Material Nr. (12NC) | 928097905115 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696416044 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718696416051 |

Dimensional drawing



| Product | D (max) | O (min) | L (min) | L (max) | L | C (max) | F (max) | F (min) | F (min) |
|----------|------------|------------|------------|------------|--------|---------|------------|------------|------------|
| MSR 200 | 13/16 | 1/4 | 1-1/2 | 1-5/8 | 1-9/16 | 3-3/16 | 1 inch | 15/16 | 15/16 |
| HR 1CT/4 | inch | inch | inch | inch | inch | inch | | inch | inch |

Photometric data



Spectral Power Distribution Colour - MSR 200 HR 1CT/4

