



MASTERColour CDM-R111

MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6

MASTERColour CDM-R111 兼备 111 mm 铝反射型卤素灯时尚外观和 MASTERColour CDM 的优点，如使用寿命长、高光效和白光明亮通透。

安全提示

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	GX8.5 [GX8.5]
操作位置	UNIVERSAL [任意或通用 (U)]
切换循环	1,000
50% 故障条件下的使用寿命 (标称)	11,000 小时
灯技术	
颜色代码	942 [CCT of 4200K]
光束角度 (标称)	40 °
发光强度 (标称)	6,700 cd
颜色名称	冷白色 (CW)
色度坐标 X (标称)	0.381
色度坐标 Y (标称)	0.370
相关色温 (标称)	4200 K
显色指数 (CRI)	96
标称使用寿命结束时灯的光通维持率 (标称)	60 %


90° 圆锥形光通量 (额定)	2,800 lm
操作和电气	
功耗	73.2 W
60% 灯光下的预热时间	120 s
电压 (标称)	92 V
电压 (标称)	92 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	反射灯
灯泡外形	R111 [R 111 毫米]

MASTERC colour CDM-R111

审批和申请	
能效等级	G
汞 (Hg) 含量 (标称)	6.3 mg
能耗 kWh/1000 h	80 kWh
产品数据	
订单产品名称	MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6
完整的产品名称	MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6


完整产品代码	871150021395210
订购代码	928098105330
材料编号 (12NC)	928098105330
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500213952
计算器 - 每个外包装箱中的包数	6
EAN/UPC - 案例	8711500213969

二维绘图




Product	D (max)	C (max)
MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6	111 mm	95 mm

光度数据




Light Distribution Diagram - MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6




Spectral Power Distribution Colour - MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6

MASTERColour CDM-R111

寿命



Life Expectancy Diagram - MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6



Lumen Maintenance Diagram - MASTERC CDM-R111 70W/942 GX8.5 40D 1CT/6

