



Architectural MSA

MSA 2500 DE UNP/1

The high luminous efficacy and optimal lamp filling of the double ended Architectural MSA lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	(P)SFC [(P)SFC]
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]
Life to 50% Failures (Nom)	2,500 h
Light Technical	
Color Code	856
Luminous Flux	250,000 lm
Chromaticity Coordinate X (Nom)	330
Chromaticity Coordinate Y (Nom)	360
Correlated Color Temperature (Nom)	5600 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	88
Arc Length O (Nom)	25 mm
Operating and Electrical	
Power Consumption	2,500 W
Lamp Current (Nom)	22.5 A

Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSA 2500 DE UNP/1
Full product name	MSA 2500 DE UNP/1
Full product code	871150020208600
Local code description	MSA2500DE
Order code	928099405103
Material Nr. (12NC)	928099405103
Local order code	MSA2500DE
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291548300
Numerator - Packs per outer box	1
EAN/UPC - Case	8711500202086


Architectural MSA

Dimensional drawing



Product	D (max)	O	C (max)
MSA 2500 DE UNP/1	41 mm	25 mm	364 mm

Photometric data



Spectral Power Distribution Colour – MSA 2500 DE UNP/1

