



MSR Gold™ FastFit

MSR Gold 700 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 h
Light Technical	
Luminous Flux	54,000 lm
Chromaticity Coordinate X (Nom)	327
Chromaticity Coordinate Y (Nom)	336
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	76 lm/W
Color rendering index (CRI)	79


Arc Length O (Nom)	3.8 mm
Operating and Electrical	
Power Consumption	700 W
Lamp Current (Nom)	10.2 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 700 FastFit 1CT/4
Full product name	MSR Gold 700 FastFit 1CT/4

MSR Gold™ FastFit

Full product code	871829122119700
Local code description	MSRG700FF
Order code	928106005115
Material Nr. (12NC)	928106005115
Local order code	MSRG700FF
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718291221197
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221203

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700 FastFit 1CT/4	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 700 FastFit 1CT/4

