

MSR Gold™ FastFit

MSR Gold™ 700 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	PGJX50	Color rendering index (CRI)	79
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	3.8 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	700 W
Luminous Flux	54,000 lm	Lamp Current (Nom)	10.2 A
Chromaticity Coordinate X (Nom)	327		
Chromaticity Coordinate Y (Nom)	336		
Correlated Color Temperature (Nom)	6000 K		

MSR Gold™ FastFit

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 700 FastFit 1CT/4
Full product name	MSR Gold™ 700 FastFit 1CT/4
Full product code	871829122119700
Order code	286914


Material Nr. (12NC)	928106005115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221197
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221203

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700	15/16	3/16	2-9/16	2-5/8	2-9/16	4-7/16	2 inch
FastFit 1CT/4	inch	inch	inch	inch	inch	inch	

Photometric data



Spectral Power Distribution Colour - MSR Gold 700 FastFit 1CT/4

