



# MSR Gold™ FastFit

## MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold<sup>TM</sup> 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)		73
Cap-Base	PGJX50 [PGJX50]	Arc Length O (Nom)		3.8 mm
Operating Position	UNIVERSAL [Any or Universal (U)]			
Life to 50% Failures (Nom)	750 hour(s)			
Light Technical				
Color Code	2			
Luminous Flux	48,000 lm			
Chromaticity Coordinate X (Nom)	298			
Chromaticity Coordinate Y (Nom)	322			
Correlated Color Temperature (Nom)	7500 K			
Luminous Efficacy (rated) (Nom)	68 lm/W			
		Operating and Electrical		
		Power Consumption		700 W
		Lamp Current (Nom)		10.2 A
		Controls and Dimming		
		Dimmable		Yes
		Product Data		
		Order product name		MSR Gold 700/2 FastFit 1CT/8

MSR Gold™ FastFit

Full product name	MSR Gold™ 700/2 FastFit 1CT/8
Full product code	872790090850300
Order code	90850300
Material Nr. (12NC)	928106205114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900908503
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900908510

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 700/2 FastFit 1CT/8	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 700/2 FastFit 1CT/8

