



MSR Gold™ FastFit

MSR Gold™ 2500/2 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	PGJX50
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	2
Luminous Flux	195,500 lm
Chromaticity Coordinate X (Nom)	301
Chromaticity Coordinate Y (Nom)	325


Correlated Color Temperature (Nom)	7200 K
Luminous Efficacy (rated) (Nom)	78 lm/W
Color rendering index (CRI)	88
Arc Length O (Nom)	9.5 mm
Operating and Electrical	
Power Consumption	2,500 W
Lamp Current (Nom)	19.53 A

MSR Gold™ FastFit

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 2500/2 FastFit 1CT/4
Full product name	MSR Gold™ 2500/2 FastFit 1CT/4
Full product code	871829122131900
Order code	287011


Material Nr. (12NC)	928106405115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221319
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221326

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 2500/2 FastFit 1CT/4	1-7/16 inch	3/8 inch	2-15/16 inch	3 inch	3 inch	6-1/16 inch	2 inch

Photometric data



Spectral Power Distribution Colour - MSR Gold 2500/2 FastFit 1CT/4

