



# MASTER SON-T PIA Plus

## MST SON-T PIA Plus 250W E E40 1SL/12

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

### Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)	
Cap-Base	E40 [E40]	102 V	
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	36,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	220 [CCT of 2000K]	Bulb Finish	Clear
Luminous Flux	32,100 lm	Bulb Shape	T46 [T 46mm]
Chromaticity Coordinate X (Nom)	0.535	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.420	Mercury (Hg) Content (Nom)	15.1 mg
Correlated Color Temperature (Nom)	2000 K	Energy Consumption kWh/1000 h	286 kWh
Luminous Efficacy (rated) (Nom)	125 lm/W	Product Data	
Arc Length O (Nom)	64 mm	Order product name	MST SON-T PIA Plus 250W E E40 1SL/12
Operating and Electrical		Full product name	MST SON-T PIA Plus 250W E E40 1SL/12
Power Consumption	257.0 W	Full product code	871829172000300
Voltage (Nom)	102 V		

# MASTER SON-T PIA Plus

Order code	928144709299
Material Nr. (12NC)	928144709299
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291720003



Numerator - Packs per outer box	12
EAN/UPC - Case	8718291720010

## Dimensional drawing



Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 250W E E40 1SL/12	48 mm	64 mm	158 mm	257 mm



## Photometric data



Light Distribution Diagram - MST SON-T PIA Plus 250W E E40 1SL/12

Spectral Power Distribution Colour - MST SON-T PIA Plus 250W E E40 1SL/12

## Lifetime



Life Expectancy Diagram - MST SON-T PIA Plus 250W E E40 1SL/12

Lumen Maintenance Diagram - MST SON-T PIA Plus 250W E E40 1SL/12

## MASTER SON-T PIA Plus

