



MASTER SON-T PIA Plus

MST SON-T PIA Plus 400W E E40 1SL/12

高压钠灯，透明外部灯泡，使用寿命长且稳定，输出较高

安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底座	E40 [E40]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	36,000 小时

灯技术	
颜色代码	220 [CCT of 2000K]
色度坐标 X (标称)	0.535
色度坐标 Y (标称)	0.420
相关色温 (标称)	2000 K
光效 (额定) (标称)	137 lm/W
弧长 O (标称)	83 mm

操作和电气	
功耗	408.0 W
电压 (标称)	105 V
电压 (标称)	105 V

控制和调光	
可调光	是

机械和外壳	
灯泡外观	透明
灯泡外形	T46 [T 46 毫米]


审批和申请	
汞 (Hg) 含量 (标称)	20 mg
能耗 kWh/1000 h	449 kWh

产品数据	
订单产品名称	MST SON-T PIA Plus 400W E E40 1SL/12
完整的产品名称	MST SON-T PIA Plus 400W E E40 1SL/12
完整产品代码	871829154772300
订购代码	928144809296
材料编号 (12NC)	928144809296
计算器 - 每包数量	1

MASTER SON-T PIA Plus



EAN/UPC - 产品/箱	8718291547723
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291547730

二维绘图



Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 400W E E40 1SL/12	48 mm	83 mm	175 mm	279 mm



光度数据



Light Distribution Diagram - MST SON-T PIA Plus 400W E E40 1SL/12

Spectral Power Distribution Colour - MST SON-T PIA Plus 400W E E40 1SL/12

寿命



Lumen Maintenance Diagram - MST SON-T PIA Plus 400W E E40 1SL/12

Life Expectancy Diagram - MST SON-T PIA Plus 400W E E40 1SL/12

MASTER SON-T PIA Plus

