



SON-T

SON-T 1000W E40 1SL/4

High Pressure Sodium lamp with clear tubular outer bulb

Warnings and Safety


- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 50% failures (nom.)	20,000 h
Light Technical	
Colour Code	220 [CCT of 2000K]
Correlated Colour Temperature	2000 K
Luminous efficacy (rated) (nom.)	130 lm/W
Colour rendering index (CRI)	-
Arc Length O (Nom)	153 mm
Operating and Electrical	
Power Consumption	960.0 W
Voltage (nom.)	100 V
Voltage (nom.)	100 V
Controls and Dimming	
Dimmable	Yes




Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T65 [T 65 mm]
Approval and Application	
Mercury (Hg) content (nom.)	23 mg
Energy consumption kWh/1,000 hours	1056 kWh
Product Data	
Order product name	SON-T 1000W E40 1SL/4
Full product name	SON-T 1000W E40 1SL/4
Full EOC	871150018412245
Order code	18412245
Material no. (12 NC)	928154509228
Local order code	1000SONT
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500184122
Numerator – packs per outer box	4
EAN/UPC – Case	8711500184139

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E40 1SL/4	66 mm	153 mm	240 mm	390 mm



Photometric data



Light Distribution Diagram - SON-T 1000W E40 1SL/4

Spectral Power Distribution Colour - SON-T 1000W E40 1SL/4

Lifetime



Life Expectancy Diagram - SON-T 1000W E40 1SL/4

Lumen Maintenance Diagram - SON-T 1000W E40 1SL/4

