



MSR

MSR 575/2 10H 1CT/4

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	GX9.5
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	47,000 lm
Chromaticity Coordinate X (Nom)	302
Chromaticity Coordinate Y (Nom)	320
Correlated Color Temperature (Nom)	6990 K
Luminous Efficacy (Rated) (Min)	75 lm/W

Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	73
Arc Length O (Nom)	7.0 mm
Operating and Electrical	
Power Consumption	575 W
Lamp Current (Nom)	6.75 A
Controls and Dimming	
Dimmable	No

Product Data	
Order product name	MSR 575/2 10H 1CT/4
Full product name	MSR 575/2 10H 1CT/4
Full product code	871829122127200
Order code	287078
Material Nr. (12NC)	928171605115


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221272
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221289

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575/2 10H 1CT/4	1-3/16 inch	5/16 inch	2-9/16 inch	2-5/8 inch	2-9/16 inch	4-15/16 inch	1-7/16 inch	1-3/8 inch	1-3/8 inch

Photometric data



Spectral Power Distribution Colour - MSR 575/2 10H 1CT/4

