



# MSR Gold™ SA Double Ended

## MSR Gold 700 SA/2 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	SFC10-4 [SFC10-4]		73
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	4.0 mm
Life to 50% Failures (Nom)	750 hour(s)	<b>Operating and Electrical</b>	
<b>Light Technical</b>		Power Consumption	700 W
Color Code	- [Not Specified]	Lamp Current (Nom)	11.5 A
Luminous Flux	48,000 lm	<b>Controls and Dimming</b>	
Chromaticity Coordinate X (Nom)	299	Dimmable	No
Chromaticity Coordinate Y (Nom)	320	<b>Product Data</b>	
Correlated Color Temperature (Nom)	7500 K	Order product name	MSR Gold 700 SA/2 DE 1CT/4
Luminous Efficacy (Rated) (Min)	62 lm/W	Full product name	MSR Gold 700 SA/2 DE 1CT/4
Luminous Efficacy (rated) (Nom)	69 lm/W		

## MSR Gold™ SA Double Ended

Full product code	871829122123400
Order code	928174705115
Material Nr. (12NC)	928174705115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221234


Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221241

### Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold 700 SA/2 DE 1CT/4	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

### Photometric data



Spectral Power Distribution Colour - MSR Gold 700 SA/2 DE 1CT/4

