



MSR Gold™ MiniFastFit (DJ/Club)

MSR Gold 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	PGJX28 [PGJX28]	Arc Length O (Nom)	5.0 mm
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	300 W
Light Technical		Lamp Current (Nom)	3.75 A
Color Code	2	Controls and Dimming	
Luminous Flux	22,700 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	288	Product Data	
Chromaticity Coordinate Y (Nom)	306	Order product name	MSR Gold 300/2 MiniFastFit 1CT/4
Correlated Color Temperature (Nom)	9300 K	Full product name	MSR Gold 300/2 MiniFastFit 1CT/4
Luminous Efficacy (Rated) (Min)	64 lm/W		
Luminous Efficacy (rated) (Nom)	75 lm/W		

MSR Gold™ MiniFastFit (DJ/Club)

Full product code	871829122111100
Order code	928177105115
Material Nr. (12NC)	928177105115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221111

Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221128

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold 300/2 MiniFastFit	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm
1CT/4						

