



MSR Gold™ MiniFastFit (DJ/Club)

MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information				
Cap-Base	PGJX28			
Operating Position	UNIVERSAL [Any or Universal (U)]			
Life to 50% Failures (Nom)	750 hour(s)			
Light Technical				
Color Code	2			
Luminous Flux	22,700 lm			
Chromaticity Coordinate X (Nom)	288			
Chromaticity Coordinate Y (Nom)	306			

Correlated Color Temperature (Nom)	9300 K
Luminous Efficacy (Rated) (Min)	64 lm/W
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	78
Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	300 W
Lamp Current (Nom)	3.75 A


Datasheet, 2023, September 19 data subject to change

MSR Gold™ MiniFastFit (DJ/Club)

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 300/2 MiniFastFit 1CT/4
Full product name	MSR Gold™ 300/2 MiniFastFit 1CT/4
Full product code	871829122111100
Order code	287177

Material Nr. (12NC)	928177105115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221111
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221128

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)
MSR Gold 300/2	15/16 inch	1/4 inch	2-5/8 inch	2-11/16 inch	2-5/8	5 inch
MiniFastFit 1CT/4					inch	

