



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


| General Information | | | |
|----------------------------|----------------------------------|------------------------------------|---------|
| Cap-Base | PGJX28 | Chromaticity Coordinate X (Nom) | 296 |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Chromaticity Coordinate Y (Nom) | 315 |
| Life to 50% Failures (Nom) | 750 hour(s) | Correlated Color Temperature (Nom) | 7500 K |
| | | Luminous Efficacy (rated) (Nom) | 64 lm/W |
| | | Color rendering index (CRI) | 70 |
| | | Arc Length O (Nom) | 3.5 mm |
| Light Technical | | | |
| Color Code | 2 | | |
| Luminous Flux | 36,800 lm | | |

MSR Gold™ MiniFastFit (Touring/Stage)

| Operating and Electrical | |
|--------------------------|-----------------------------------|
| Power Consumption | 575 W |
| Lamp Current (Nom) | 10.2 A |
| Controls and Dimming | |
| Dimmable | Yes |
| Product Data | |
| Order product name | MSR Gold 575/2 MiniFastFit 1CT/4 |
| Full product name | MSR Gold™ 575/2 MiniFastFit 1CT/4 |


| | |
|---------------------------------|-----------------|
| Full product code | 871829122109800 |
| Order code | 287201 |
| Material Nr. (12NC) | 928184005115 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291221098 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718291221104 |

Dimensional drawing



| Product | D | O | L (min) | L | L | C | F | F | F (min) |
|----------------------------------|---------------|--------------|----------------|---------------|---------------|----------------|----------------|----------------|----------------|
| | (max) | | | (max) | | (max) | (max) | | |
| MSR Gold 575/2 MiniFastFit 1CT/4 | 15/16 inch | 3/16 inch | 2-3/16 inch | 2-1/4 inch | 2-1/4 inch | 4-7/16 inch | 1-7/16 inch | 1-7/16 inch | 1-7/16 inch |

Photometric data



Spectral Power Distribution Colour - MSR Gold 575/2 MiniFastFit 1CT/4

