



MASTERColour CDM-Tm Elite Mini

MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

Mini, single-ended, very high-efficiency, long-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high color rendering

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- For 50W use with Philips electronic gear only
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底座	GU6.5
操作位置	UNIVERSAL [任意或通用 (U)]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	20,000 小时
灯技术	
颜色代码	930 [CCT of 3000K]
光通量	3,950 lm
颜色名称	暖白色 (WW)
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K


光效 (额定) (标称)	102 lm/W
显色指数 (CRI)	90
弧长 Ø (标称)	4.7 mm
操作和电气	
功耗	39.1 W
电压 (标称)	87 V
电压 (标称)	87 V
控制和调光	
可调光	否

MASTERColour CDM-Tm Elite Mini

机械和外壳	
灯泡外观	透明
灯泡外形	T13.3 [T 13.3 毫米]
审批和申请	
能效等级	F
汞 (Hg) 含量 (最高)	4.7 mg
汞 (Hg) 含量 (标称)	4.7 mg
能耗 kWh/1000 h	40 kWh
EPREL 注册号	1519237
产品数据	
订单产品名称	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT



完整的产品名称	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT
完整产品代码	871829115382500
订购代码	928187405130
材料编号 (12NC)	928187405130
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8718291153825
计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8718291153832

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT	13.3 mm	0.5 in	4.7 mm	28 mm	32 mm	30 mm	56.7 mm

光度数据



Light Distribution Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT


Spectral Power Distribution Colour - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

MASTERColour CDM-Tm Elite Mini

寿命



Life Expectancy Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT



Lumen Maintenance Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

