



MASTERColour CDM-Rm Elite Mini

CDM-Rm Elite Mini 35W/942 GX10 MR16 10D

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high color rendering

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GX10 [GX10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Switching Cycle	1,350
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	942 [CCT of 4200K]
Beam Angle (Nom)	10 degree(s)
Luminous Intensity (Nom)	20,500 cd
Chromaticity Coordinate X (Nom)	0.377
Chromaticity Coordinate Y (Nom)	0.377
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	57.5 lm/W
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	73 %


Luminous Flux in 90° Cone (Rated)	2,000 lm
Operating and Electrical	
Power Consumption	39 W
Warm-up time to 60% light	120 s
Voltage (Nom)	90 V
Voltage (Nom)	90 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Mercury (Hg) Content (Nom)	4.7 mg

MASTERCoulour CDM-Rm Elite Mini

Energy Consumption kWh/1000 h	43 kWh
Product Data	
Order product name	CDM-Rm Elite Mini 35W/942 GX10 MR16 10D
Full product name	CDM-Rm Elite Mini 35W/942 GX10 MR16 10D
Full product code	871829169177800
Order code	928190505330

Material Nr. (12NC)	928190505330
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291691778
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291691785


Dimensional drawing



Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 35W/942 GX10 MR16 10D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm

Photometric data


Light Distribution Diagram - CDM-Rm Elite Mini 35W/942 GX10 MR16 10D




Spectral Power Distribution Colour - CDM-Rm Elite Mini 35W/942 GX10 MR16 10D

MASTERColour CDM-Rm Elite Mini

Lifetime



Life Expectancy Diagram - CDM-Rm Elite Mini 35W/942 GX10 MR16 10D



Lumen Maintenance Diagram - CDM-Rm Elite Mini 35W/942 GX10 MR16 10D

