



MSD Gold™ MiniFastFit

MSD Gold™ 300/2 MiniFastFit 1CT/16

The specially designed lamp base of the MSD Gold™ MiniFastFit means that this lamp can be replaced in just seconds, helping to ensure non-stop entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. The lamp's compact size allows for easy handling and compact fixture designs, while the very short arc provides a high perceived brightness and high beam intensity. What's more, the MSD Gold™ MiniFastFit has an extended lifetime, which further reduces lamp replacement costs.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	PGJX28 [PGJX28]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	21,000 lm
Chromaticity Coordinate X (Nom)	292
Chromaticity Coordinate Y (Nom)	310
Correlated Color Temperature (Nom)	8600 K
Luminous Efficacy (rated) (Nom)	70 lm/W


Color rendering index (CRI)	73
Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	300 W
Lamp Current (Nom)	3.8 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD Gold 300/2 MiniFastFit 1CT/16

MSD Gold™ MiniFastFit

Full product name	MSD Gold™ 300/2 MiniFastFit 1CT/16
Full product code	872790091257900
Order code	91257900
Material Nr. (12NC)	928199805114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900912579
Numerator - Packs per outer box	16
EAN/UPC - Case	8727900912586

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSD Gold 300/2 MiniFastFit 1CT/16	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

Photometric data



Spectral Power Distribution Colour - MSD Gold 300/2 MiniFastFit 1CT/16

