



MASTER HPI Plus

MASTER HPI Plus 400W/645 BUS-P E40 1SL/6

Quartz metal halide lamps with opalized outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom) 125 V	
Cap-Base	E40 [E40]	Controls and Dimming	
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Dimmable	No
Life to 50% Failures (Nom)	20,000 hour(s)	Mechanical and Housing	
Light Technical		Bulb Finish	Coated glass
Color Code	645 [CCT of 4500K]	Bulb Shape	ED37
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	367	Mercury (Hg) Content (Nom)	67.2 mg
Chromaticity Coordinate Y (Nom)	374	Energy Consumption kWh/1000 h	434 kWh
Correlated Color Temperature (Nom)	4500 K	Product Data	
Luminous Efficacy (rated) (Nom)	82 lm/W	Order product name	MASTER HPI Plus 400W/645 BUS-P E40 1SL/6
Color rendering index (CRI)	65	Full product name	MASTER HPI Plus 400W/645 BUS-P E40 1SL/6
Operating and Electrical		Full product code	871150021145310
Power Consumption	395.0 W	Order code	928410700027
Voltage (Nom)	125 V		

MASTER HPI Plus

Material Nr. (12NC)	928410700027
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500211453
Numerator - Packs per outer box	6

EAN/UPC - Case	8711500211460
----------------	---------------

Dimensional drawing




Product	D (max)	C (max)
MASTER HPI Plus 400W/645 BUS-P E40 1SL/6	122 mm	290 mm

Photometric data



Spectral Power Distribution Colour - MASTER HPI Plus 400W/645 BUS-P E40 1SL/6

Lifetime



Life Expectancy Diagram - MASTER HPI Plus 400W/645 BUS-P E40 1SL/6



Lumen Maintenance Diagram - MASTER HPI Plus 400W/645 BUS-P E40 1SL/6

MASTER HPI Plus

