



Barco digital cinema projectors


XDC-1200B

Digital Xenon Cinema B-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Barco projectors. There is a choice of three power ratings in the B-type Digital Xenon Cinema lamps range: 3000W, 4000W, or 6500W. There is also a choice of three power ratings in the BH-type Digital Helios lamps: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to B-type Digital Cinema Xenon lamps there are C-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Product data

General Information		Full product name	
Operating Position	P5 [Parallel +/-5D or Horizontal(HOR)]	Full product code	XDC-1200B
Nominal lifetime	3,000 h	Order code	871829176659900
Operating and Electrical		Material Nr. (12NC)	928418506301
Power Consumption	1,200 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	60 A	EAN/UPC - Product/Case	8718291766599
Voltage (Nom)	20 V	Numerator - Packs per outer box	1
Voltage (Nom)	20 V	EAN/UPC - Case	8718291766605
Product Data			
Order product name	XDC-1200B		

Dimensional drawing



Product	O	D	X	B (max)	C (max)	A
XDC-1200B	4.7 mm	46 mm	132 mm	294 mm	343 mm	123 mm

