



Barco digital cinema projectors

XDC-6500BL

Digital Xenon Cinema B-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Barco projectors. There is a choice of three power ratings in the B-type Digital Xenon Cinema lamps range: 3000W, 4000W, or 6500W. There is also a choice of three power ratings in the BH-type Digital Helios lamps: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to B-type Digital Cinema Xenon lamps there are C-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Product data

General Information	
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]
Nominal lifetime	600 hour(s)


Operating and Electrical	
Power Consumption	6,501 W
Lamp Current (Nom)	162 A
Voltage (Nom)	40 V
Voltage (Nom)	40 V

Product Data	
Full product code	871869645421300

Order product name	XDC-6500BL
Order code	928418706301
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	928418706301
Full product name	XDC-6500BL
EAN/UPC - Case	8718696454220
EAN/UPC - Product/Case	8718696454213

Barco digital cinema projectors

Dimensional drawing



Product	O	D	X	B (max)	C (max)	A
XDC-6500BL	8.6 mm	70 mm	152 mm	376 mm	409 mm	158 mm

