

# Christie digital cinema projectors


## XDC 3000CL

Digital Xenon Cinema C-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Christie projectors. There is a choice of four power ratings in the C-type Digital Cinema Xenon lamps range: 2000W, 3000W, 4500W, or 6000W. There is also a choice of three power ratings in the CH-type Digital Helios lamps range: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to C-type Digital Cinema Xenon lamps there are B-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

### Product data

Operating and Electrical			
Power Consumption	3,000 W	Order code	928419406301
Lamp Current (Nom)	110 A	Numerator - Quantity Per Pack	1
Voltage (Nom)	29 V	Numerator - Packs per outer box	1
Voltage (Nom)	29 V	Material Nr. (12NC)	928419406301
		Full product name	XDC 3000CL
		EAN/UPC - Case	8718696594186
		EAN/UPC - Product/Case	8718696594179
Product Data			
Full product code	871869659417900		
Order product name	XDC 3000CL		

Dimensional drawing



Product	O	D	B (max)	C (max)	A
XDC 3000CL	5.7 mm	60 mm	351 mm	397 mm	162 mm

