



MHN-TD Essential

MHN-TD Essential 150W/730 Rx7s 1CT/12

高光效型双端防紫外石英金卤灯

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	RX7S [RX7s]
50% 故障条件下的使用寿命 (标称)	8,000 小时
灯技术	
颜色代码	730 [CCT of 3000K]
颜色名称	暖白色 (WW)
色度坐标 X (标称)	434
色度坐标 Y (标称)	400
相关色温 (标称)	3000 K
光效 (额定)(标称)	87 lm/W
显色指数 (CRI)	70
弧长 O (标称)	17.8 mm
操作和电气	
功耗	150.0 W
电压 (标称)	96 V


电压 (标称)	96 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	透明
灯泡材料	玻璃
灯泡外形	T24 [T 24 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	18 mg
能耗 kWh/1000 h	165 kWh
产品数据	
订单产品名称	MHN-TD Essential 150W/730 Rx7s 1CT/12
完整的产品名称	MHN-TD Essential 150W/730 Rx7s 1CT/12
完整产品代码	872790084522800

MHN-TD Essential

订购代码	928481100192
材料编号 (12NC)	928481100192
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8727900845228


计算器 - 每个外包装箱中的包数	12
EAN/UPC - 案例	8727900845235

二维绘图




Product	O
MHN-TD Essential 150W/730 Rx7s 1CT/12	17.8 mm

光度数据




Light Distribution Diagram - MHN-TD Essential 150W/730 Rx7s 1CT/12




Spectral Power Distribution Colour - MHN-TD Essential 150W/730 Rx7s 1CT/12

寿命



Life Expectancy Diagram - MHN-TD Essential 150W/730 Rx7s 1CT/12



Lumen Maintenance Diagram - MHN-TD Essential 150W/730 Rx7s 1CT/12

