



# MASTER HPI-T Plus

## HPI-T Plus 400W/645 E40 1SL/12

Quartz metal halide lamps with clear outer bulb

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	P20 [Parallel +/-20D or Horizontal(HOR)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	645 [CCT of 4500K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	361
Chromaticity Coordinate Y (Nom)	372
Correlated Color Temperature (Nom)	4500 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	65
Arc Length O (Nom)	30.5 mm
Operating and Electrical	
Power Consumption	385 W
Voltage (Nom)	125 V


Voltage (Nom)	125 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T46 [T 46mm]
Approval and Application	
Mercury (Hg) Content (Nom)	29.5 mg
Energy Consumption kWh/1000 h	424 kWh
Product Data	
Order product name	HPI-T Plus 400W/645 E40 1SL/12
Full product name	HPI-T Plus 400W/645 E40 1SL/12
Full product code	871829167613300
Order code	928481600095

MASTER HPI-T Plus

Material Nr. (12NC)	928481600095
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291676133
Numerator - Packs per outer box	12


EAN/UPC - Case	8718291676140
----------------	---------------

Dimensional drawing




Product	D (max)	O	L	C (max)
HPI-T Plus 400W/645 E40 1SL/12	47 mm	30.5 mm	168 mm	286 mm

Photometric data




Light Distribution Diagram - HPI-T Plus 400W/645 E40 1SL/12




Spectral Power Distribution Colour - HPI-T Plus 400W/645 E40 1SL/12

Lifetime



Life Expectancy Diagram - HPI-T Plus 400W/645 E40 1SL/12



Lumen Maintenance Diagram - HPI-T Plus 400W/645 E40 1SL/12

## MASTER HPI-T Plus

