



HPI-T

HPI-T 1000W/543 E40 1SL/4

带透明外部灯泡的石英金属卤化物灯

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	E40 [E40]
操作位置	P [并行或水平 (HOR)]
50% 故障条件下的使用寿命 (标称)	12,000 小时

灯技术	
颜色代码	543 [CCT of 4300K]
颜色名称	冷白色 (CW)
色度坐标 X (标称)	370
色度坐标 Y (标称)	380
相关色温 (标称)	4300 K
光效 (额定) (标称)	83 lm/W
显色指数 (CRI)	57
弧长 O (标称)	80 mm

操作和电气	
功耗	990 W
电压 (标称)	130 V

电压 (标称)	130 V
---------	-------

控制和调光	
可调光	否

机械和外壳	
灯泡外观	透明
灯泡外形	T65 [T 65 毫米]

审批和申请	
汞 (Hg) 含量 (标称)	86 mg
能耗 kWh/1000 h	1089 kWh


产品数据	
订单产品名称	HPI-T 1000W/543 E40 1SL/4
完整的产品名称	HPI-T 1000W/543 E40 1SL/4
完整产品代码	692234199953600
订购代码	928482600093

HPI-T

材料编号 (12NC)	928482600093
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6922341999536
计算器 - 每个外包装箱中的包数	4


EAN/UPC - 案例	6922341993145
--------------	---------------

二维绘图




Product	D (max)	O	L	C (max)
HPI-T 1000W/543 E40 1SL/4	66 mm	80 mm	240 mm	382 mm

光度数据




Spectral Power Distribution Colour - HPI-T 1000W/543 E40 1SL/4

寿命



Life Expectancy Diagram - HPI-T 1000W/543 E40 1SL/4



Lumen Maintenance Diagram - HPI-T 1000W/543 E40 1SL/4

