



MASTER HPI-T Plus

MASTER HPI-T Plus 250W/643 E39 1SL

Quartz metal halide lamps with clear outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	P20 [Parallel +/-20D or Horizontal(HOR)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	645 [CCT of 4500K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	365
Chromaticity Coordinate Y (Nom)	377
Correlated Color Temperature (Nom)	4500 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	69
Arc Length O (Nom)	29 mm
Operating and Electrical	
Power Consumption	245 W
Voltage (Nom)	128 V


Voltage (Nom)	128 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T46 [T 46mm]
Approval and Application	
Mercury (Hg) Content (Nom)	36 mg
Product Data	
Order product name	MASTER HPI-T Plus 250W/643 E39 1SL
Full product name	MASTER HPI-T Plus 250W/643 E39 1SL
Full product code	872790082916700
Order code	928483400191
Material Nr. (12NC)	928483400191

MASTER HPI-T Plus

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900829167
Numerator - Packs per outer box	12


EAN/UPC - Case	8727900829174
----------------	---------------

Dimensional drawing




Product	D (max)	O	L	C (max)
MASTER HPI-T Plus 250W/643 E39 1SL	47 mm	29 mm	152 mm	252 mm

Photometric data




Light Distribution Diagram - MASTER HPI-T Plus 250W/643 E39 1SL




Spectral Power Distribution Colour - MASTER HPI-T Plus 250W/643 E39 1SL

Lifetime



Life Expectancy Diagram - MASTER HPI-T Plus 250W/643 E39 1SL



Lumen Maintenance Diagram - MASTER HPI-T Plus 250W/643 E39 1SL

MASTER HPI-T Plus

