



Switch Start Metal Halide Protected

MH 100W/640 E26 CL

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	H [Hanging or Base Up (BU)]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	385
Chromaticity Coordinate Y (Nom)	390
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	65
Operating and Electrical	
Power Consumption	106 W


Voltage (Nom)	100 V
Voltage (Nom)	100 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ED17
Approval and Application	
Mercury (Hg) Content (Nom)	10.2 mg
Energy Consumption kWh/1000 h	110 kWh
Product Data	
Order product name	MH 100W/640 E26 CL

Switch Start Metal Halide Protected

Full product name	MH 100W/640 E26 CL
Order code	928485900194
Material Nr. (12NC)	928485900194
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677460785

Numerator - Packs per outer box	3
EAN/UPC - Case	50046677460780

Dimensional drawing



Product	D (max)	L (min)	C (max)
MH 100W/640 E26 CL	56 mm	83 mm	138 mm

