



MASTERColour CDM-BU

MASTERColour CDM-BU 210W/942 E40 1CT/12

Ceramic metal-halide lamps with opalized outer bulb, providing quality light and low energy consumption.

Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	H45 [h45]
Life to 50% Failures (Nom)	20,000 hour(s)

Light Technical	
Color Code	942 [CCT of 4200K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	377
Chromaticity Coordinate Y (Nom)	371
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	90

Operating and Electrical	
Power Consumption	210.0 W
Voltage (Nom)	100 V
Voltage (Nom)	100 V

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Shape	ED90 [ED 90mm]

Approval and Application	
Mercury (Hg) Content (Nom)	23 mg
Energy Consumption kWh/1000 h	231 kWh

Product Data	
Order product name	MASTERColour CDM-BU 210W/942 E40 1CT/12
Full product name	MASTERColour CDM-BU 210W/942 E40 1CT/12
Full product code	692059027688000
Order code	928489800191
Material Nr. (12NC)	928489800191
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6920590276880
Numerator - Packs per outer box	12
EAN/UPC - Case	6920590276897

MASTERCcolour CDM-BU

Dimensional drawing



Product	D (max)	C (max)
MASTERCcolour CDM-BU 210W/942 E40 1CT/12	91 mm	226 mm

